

磷脂隆 A-OSL



磷酸化加脂剂

成份

磷脂隆 A-OSL 是一种稳定性很好的磷酸化加脂剂。

使用在回水浴中，磷脂隆 A-OSL 提高皮革撕裂强度。

磷脂隆 A-OSL 适合浸酸，铬复鞣，复鞣浴使用，对盐，酸及铬，铝稳定。

磷脂隆 A-OSL 产生软及重量轻皮革。

磷脂隆 A-OSL 可用于加强其他加脂剂稳定性。

为了达到最好的效果 磷脂隆 A-OSL 要预先加热到 25-35C，再把它乳化到 40-50C 的水之中。

应用范围

A. 羊皮服装革：2-3% 磷脂隆 A-OSL.

B. 家俱革：1.5-2% 磷脂隆 A-OSL.

C. 软鞋面革：1-1.5% 磷脂隆 A-OSL.

D. 箱包革：至 2% 磷脂隆 A-OSL.

特性

外观:	棕色液体
分析:	pH 5.0-6.5
有效成份:	60-64%
电性:	阴离子
稳定性:	用于浸酸，铬复鞣，复鞣浴。对铬，铝稳定。
储存方法:	室温。如出现霜冻，搅拌均匀即可。 存放在阴凉及通风的库房。
保质期:	密封容器约 12 月。

包装

120KGS 塑料桶

The information and technical advice are provided to you 'as is' and the Company expressly disclaims all warranties of any kind, either implied or expressed. You agree to indemnify and hold harmless the Company and its representatives, subsidiaries, affiliates, related parties, officers, directors, employees, agents from any claim or demand, including reasonable legal fees, that may be filed by any third party, arising out of your conduct or connection with the use of "Product Literature" or "Technical Information" or "Technical Advice" or "Technical Guidance" or any "Recommendation".